

In view of our current ecological and economic challenges it becomes apparent: Honing with diamond or boron nitride cutting shoes is indispensable in modern production processes.

Numerous factors determine the honing result. The ideal composition of the honing stone and all other influencing factors to the honing process need to be coordinated in order to achieve optimal end results. High production quality, short cycle times and longevity of the tools are achieved this way.

Defining a suitable honing stone is the task of our specialists with many years of practical experience in the most diverse of applications in the entire field of honing technology.



Honing stone

In principle, the perfect honing stone consists of three different main components, which offer the required cutting properties as a uniform whole.

The basis and thus the most important component of each honing stone is the abrasive. Synthetic diamonds or cubic boron nitride (CBN) in various grit sizes are used.


The second component is the metal bonding which is responsible for the proper adhesion of the abrasive crystals warranting excellent wear performance.

The copper-plated steel blank is the third and last component and is the support material of each stone in a drawn, galvanized form.









Standard honing stone

The abrasive layer is produced with a steel blank and the honing stone is soldered or bonded onto the stone holder of the tool.

How to order: W x H x L x Y Example: 5.00 x 6.00 x 100.00 x 2.0

Slotted standard honing stone

The same structure as for the standard honing stone only with longitudinally slotted abrasive. How to order: W x H x L x Y x S Example: 6.00 x 6.00 x 80.00 x 2.5 S 2.0

Solid honing stone


Consists only of an abrasive layer without a steel blank and is also soldered or bonded onto the stone holder/holder segment of the tool.


How to order: W x H x L x Y Example: 3.00 x 2.00 x 60.00 x 2.0

Standard honing stone type T

Stone with T-shaped profile with a narrow reduced section and a short wide work element in the lower area.

How to order: W x H x L x Y G x L' Example: 3.00 x 3.00 x 45.00 x 2.0 G 7.5






Compact honing stone

A ready to be installed stone for direct use in the tool body. This stone type is used in tooling systems for the machining of high precision bores.

In general, the structural form is rounded angular.


How to order: W x H x L x Y Stone drawings required

Example: 3.00 x 7.40 x 40.00 x 1.0




Standard/compact or solid honing stone type G

Honing stone with upper and lower guide arranged symmetrically How to order: W x H x L x Y G x L' Example: 3.00 x 3.00 x 45.00 x 2.0 G 7.5




Solid honing stone type P

Honing stone with narrow cutting part and lateral guides which are arranged symmetrically. Application. Cylinder block and bushings
How to order: W x H x L x Y P W'
Example: 6.00 x 5.00 x 80.00 x 2.0 P 1.5
(Stone width W not equal to stone height H)



To round off our product portfolio, we also offer ceramic honing stones. For detailed information please contact our specialists.



The specification

defines the exact composition of the respective abrasive layer of each honing stone. Each individual component directly influences the cutting characteristics and quality of the bores to be honed. In principle, four components need be taken into account.

The concentration

describes the number of carats of diamond or boron nitride crystal per ${\rm cm^3}$ in the abrasive layer.

The type of bond

and its characteristics are determined by the stability of shape, the wear performance and the adhesion of the cutting crystal. Whether a bond has to be hard, tough or brittle depends on the material which is to be honed.

The types of crystal

ding on the process parameters for the diamond synthesis. They differ in color, hardness, form, structure and stability. These characteristics also determine the cutting behavior of each respec-


are available in various forms depen-

The grit size

low surface profiles.

tive crystal.

generally determines the achievable depth of roughness or surface profile and is responsible for the stock removal capacity of the honing stone. This means that "coarse" grit sizes are used for rough honing in order to be able to make use of the high cutting efficiency. In the case of finish honing on the other hand, "fine" grit sizes are used to obtain



Microscope image: Individual crystals



Microscope image: Bonding material

Trust in the technology leader with many years' experience and global presence! Innovative technology combined with an economical mindset sets us apart.

